

1250 Sheppard Ave. West Toronto, ON M3K 2A6 **T** 1.800.387.3713 **F** 416.661.3447

order@waynesafety.com

www.waynesafety.com

# **15I-761PF** Biodegradable Nitrile Exam Gloves

Providing a green solution for nitrile glove disposal



#### Guard your health Protect the environment

Wayne Safety's biodegradable nitrile exam gloves is one of our latest initiatives in supporting sustainable development and creating a greener environment. It contains an organic additive to accelerate the biodegradation rate of the gloves in an anaerobic environment, allowing the gloves to microbially degrade in landfills and reduce waste accumulation.



## Product Advantages:

- The biodegradability of the gloves is proven using the internationally recognized standard ASTM D5511.
- The glove will maintain its physical properties for 3 years under normal storage conditions. Biodegradation process starts only when surrounded by microorganisms in terrestrial environment.
- Manufactured under ISO 9001 and ISO 13485 quality management systems in accordance with ASTM D6319 and EN455 standards

## **Product Features :**

- Medical Grade Health Canada Class 2 License
- Approved for use with Chemotherapy Drugs and Fentanyl Citrate ASTM D6978
- Gloves are elastic and comfortable reducing hand fatigue
- Textures at fingers ensure increased grip
- 100% free of natural latex
- Ambidextrous
- Rolled edges for easy donning

#### **Glove Performance :**

Product Sizes: XS, S, M, L, XL, XXL Product Colour: Apple Green

<b>Physical Properties</b>	Typical Values		<b>Testing Method</b>
Weight(M)(+/-0.2g)	3.5		/
Palm Thickness (mm)(min)	0.06		ASTM D3767
Finger Thickness (mm)(min)	0.08		ASTM D3767
Length (mm)	240		ASTM D3767,EN455-2
Freedom from Holes	AQL1.5		ASTM D5151,EN 455-1
Width(+/-5mm)	X-Small=75mm Small=80mm Medium=95mm Large=110mm X-Large=120mm XX- Large=130mm		ASTM D6319,EN455-2
Powder-free Residue(mg)	Not more than 2mg per glove		ASTM D6124, EN455-3
	<b>BEFORE AGING</b>	AFTER AGING	
Tensile Strength (MPa)(min)	16	14	ASTM D412& D573
Ultimate Elongation (%)(min)	500	400	ASTM D412& D573
Force at break (N)(median)	6	6	EN 455-2
ette utation with the sta			